

Инв. № дубляжата

Инв. № подлинника

1080

Лит.изм.

2

№ изв.

11776

Размеры, мм

| Наружный диаметр трубы D_H | d | d_1 $\pm 0,2$ | D | l | Наружный диаметр трубы D_{H1} | d_2 | d_3 $\pm 0,2$ | D_1 | D_3 | S | l_1 | l_2 | L | Масса 100 шт., кг | | | | |
|------------------------------|-----|--------------------|----------|-----|---------------------------------|-------|--------------------|----------|-------|------|-------|-------|-----|-------------------|----|----|----|------|
| 6 | 4 | 11 | MR14:1,5 | 13 | 8 | 6 | 13,0 | MR16:1,5 | 19,6 | 17 | 13 | 16 | 32 | 1,83 | | | | |
| | | | | | 10 | 8 | 15,0 | MR18:1,5 | 21,9 | 19 | | | | 2,06 | | | | |
| | | | | | 12 | 10 | 17,0 | MR20:1,5 | 25,4 | 22 | | | | 2,38 | | | | |
| 8 | 6 | 13 | MR16:1,5 | | 10 | 5 | 15,0 | MR18:1,5 | 21,9 | 19 | | | | 2,18 | | | | |
| | | | | | 12 | 10 | 17,0 | MR20:1,5 | 25,4 | 22 | | | | 2,52 | | | | |
| | | | | | 14 | 12 | 19,0 | MR22:1,5 | 27,7 | 24 | | | | 2,94 | | | | |
| 10 | 8 | 15 | MR18:1,5 | | 12 | 10 | 17,0 | MR20x1,5 | 25,4 | 22 | | | | 2,62 | | | | |
| | | | | | 14 | 12 | 19,0 | MR22:1,5 | 27,7 | 24 | | | | 3,08 | | | | |
| | | | | | 16 | 14 | 21,0 | MR24:1,5 | 31,2 | 27 | | | | 3,78 | | | | |
| 12 | 10 | 17 | MR20:1,5 | | 14 | 12 | 19,0 | MR22:1,5 | 27,7 | 24 | | | | 3,27 | | | | |
| | | | | | 16 | 14 | 21,0 | MR24x1,5 | 31,2 | 27 | | | | 3,92 | | | | |
| | | | | | 18 | 16 | 24,0 | MR27:1,5 | 34,6 | 30 | | | | 4,52 | | | | |
| 14 | 12 | 19 | MR22:1,5 | | 16 | 14 | 21,0 | MR24x1,5 | 31,2 | 27 | | | | 3,85 | | | | |
| | | | | 18 | 16 | 24,0 | MR27:1,5 | 34,6 | 30 | 4,49 | | | | | | | | |
| | | | | 20 | 18 | 27,0 | MR30x1,5 | 36,9 | 32 | 5,19 | | | | | | | | |
| 16 | 14 | 21 | MR24x1,5 | 15 | 18 | 16 | 24,0 | MR27:1,5 | 34,6 | 30 | 15 | 18 | 35 | 5,11 | | | | |
| | | | | | 20 | 18 | 27,0 | MR30:1,5 | 36,9 | 32 | | | | 5,38 | | | | |
| | | | | | 22 | 20 | 29,0 | MR33:1,5 | 41,6 | 36 | | | | 5,72 | | | | |
| 18 | 16 | 24 | MR27:1,5 | | 18 | 16 | 24,0 | MR27:1,5 | 34,6 | 30 | | | | 5,11 | | | | |
| | | | | | 20 | 18 | 27,0 | MR30:1,5 | 36,9 | 32 | | | | 5,38 | | | | |
| | | | | | 22 | 20 | 29,0 | MR33:1,5 | 41,6 | 36 | | | | 5,72 | | | | |
| | | | | | | | | | | | | | | | 16 | 19 | 40 | 7,06 |

ОСТ 110355-72 стр. 3

| | |
|----------------|------|
| Ив. № дубината | |
| Ив. № подаяния | 1080 |

| | | | | | | | | | | | | | |
|----------|------|-------|--|--|--|--|--|--|--|--|--|--|--|
| Лит.изм. | 1 | 2 | | | | | | | | | | | |
| № изв. | 6628 | 11776 | | | | | | | | | | | |

Размеры, мм

Продолжение

| Наружный диаметр трубы D_H | d | d_1 $\pm 0,2$ | D | b | Наружный диаметр трубы D_{H1} | d_2 | d_3 $\pm 0,2$ | D_1 | D_3 | S | b_1 | b_2 | L | Масса 100 шт., кг |
|------------------------------|-----|--------------------|----------|-----|---------------------------------|-------|--------------------|----------|-------|-----|-------|-------|-----|-------------------|
| 20 | 18 | 27 | MR30x1,5 | 15 | 22 | 20 | 29,0 | MR33x1,5 | 41,6 | 36 | 16 | 19 | 40 | 7,20 |
| | | | | | 25 | 23 | 32,0 | MR36 1,5 | | | | | | 6,91 |
| 22 | 20 | 29 | MR33x1,5 | 16 | 28 | 26 | 35,0 | MR39x1,5 | 47,3 | 41 | 17 | 20 | 42 | 7,41 |
| | | | | | 30 | 28 | 35,5 | | | | | | | 8,37 |
| 25 | 23 | 32 | MR36x1,5 | 17 | 32 | 30 | 38,0 | MR42x1,5 | 53,1 | 46 | 17 | 20 | 42 | 8,41 |
| | | | | | 30 | 28 | 35,5 | | | | | | | 9,22 |
| 28 | 26 | 35 | MR39x1,5 | 17 | 32 | 30 | 38,0 | MR42x1,5 | 53,1 | 46 | 17 | 20 | 42 | 8,83 |
| | | | | | 32 | 30 | 38,0 | | | | | | | 10,21 |

ОСТ 10355-72 Спр. 4

